

## 球形氧化铝/Spherical Alumina Powder BAK-30

➤ 高球化率, 高填充率, 高热导率, 低离子含量。/High Spheroidization Ratio, High Filling Ratio, High Thermal Conductivity, Trace Ionic Impurities.

➤ 应用/Application

热界面材料, 导热工程塑料, 导热基板。/Thermal Interface Materials, Thermal Plastics, Thermal Clads.

➤ 物理特性/Physical Characteristics

项目 /Item	单位 /Unit	典型值 /Typical Value	方法/设备 Method/Device
粒度/Particle Size	(D <sub>10</sub> ) μm	16.88	Light Scattering/OMEC LS-POP(6)
	(D <sub>50</sub> ) μm	30.52	
	(D <sub>90</sub> ) μm	48.87	
粒度/Particle Size	(D <sub>10</sub> ) μm	20.42	Light Scattering/HORIBA LA-950v2
	(D <sub>50</sub> ) μm	33.23	
	(D <sub>90</sub> ) μm	51.02	
比表面积/S.S.A.	m <sup>2</sup> /g	0.15	3H-2000A Specific Surface Area Analyzer
电导率/Electrical Conductivity	μS/cm	7.95	Mettler FE-30 Conductivity Meter
pH	-	7.10	Mettler FE-20 pH Meter
含湿率/Moisture	%	0.03	Halogen water-determination meter / (110°C/10min)
真密度/True Density	g/cm <sup>3</sup>	3.62	3H-2000TD True Density Analyzer
球化率/ Spheroidization	%	98	Microscopic Observation

➤ 化学成份/Chemical Characteristics

项目 /Item	单位 /Unit	典型值 /Typical Value	方法/设备 Method/Device
化学成分/Chemical Composition	Al <sub>2</sub> O <sub>3</sub> %	99.93	1-Fe <sub>2</sub> O <sub>3</sub> -Na <sub>2</sub> O-SiO <sub>2</sub> -Loss
	SiO <sub>2</sub> ppm	20	ICP
	Fe <sub>2</sub> O <sub>3</sub> ppm	60	ICP
	Na <sub>2</sub> O ppm	90	ICP
	Loss %	0.05	1100°C/2h

➤ SEM Image

